



# ENAPART



93 S Railroad Avenue Unit C  
Bergenfield NJ 07621 USA  
[www.enapart.com](http://www.enapart.com)  
[sales@enapart.com](mailto:sales@enapart.com)



Via del Canneto 35,  
Borgosatollo, Brescia - Italia  
[www.enapart.it](http://www.enapart.it)  
[vendite@enapart.it](mailto:vendite@enapart.it)



Barbaros Mah. Ihlamur Bul. Aĝaoĝlu  
My Newwork No:3/15 Ataşehir / İstanbul  
[www.enapart.net](http://www.enapart.net)  
[satis@enapart.net](mailto:satis@enapart.net)



PRIVADA 10 B SUR #3908 COL.  
ANZUREZ, C.P. 72530, PUEBLA, PUE  
[www.enapart.com.mx](http://www.enapart.com.mx)  
[sales@enapart.com.mx](mailto:sales@enapart.com.mx)



Friedrich-Ebert-Anlage 36, 60325  
Frankfurt am Main, Germany  
[www.enapart.de](http://www.enapart.de)  
[anfrage@enapart.de](mailto:anfrage@enapart.de)



4 boulevard Carnot, 95400  
villiers-le-bel, Paris, France  
[www.enapart.fr](http://www.enapart.fr)  
[sales@enapart.fr](mailto:sales@enapart.fr)



65049, ОДЕСА, ВУЛИЦЯ ІВАНА  
ФРАНКА, БУДИНОК 55, ПОВЕРХ 3  
[www.enapart.com.ua](http://www.enapart.com.ua)  
[sales@enapart.com.ua](mailto:sales@enapart.com.ua)



MUNICIPIUL BUCUREȘTI, SECTOR 3,  
B-DUL BASARABIA, NR.250, CORP P+5  
[www.enapart.ro](http://www.enapart.ro)  
[sales@enapart.ro](mailto:sales@enapart.ro)



〒584-0023 大阪府富田林市若松町  
東2丁目2番16号  
[www.enapart.co.jp](http://www.enapart.co.jp)  
[sales@enapart.co.jp](mailto:sales@enapart.co.jp)



PLAZA NUESTRA SEÑORA DE LAS  
NIEVES 12 ,LOCAL ,50012,ZARAGOZA  
[www.enapart.es](http://www.enapart.es)  
[ventas@enapart.es](mailto:ventas@enapart.es)



Складова база „Онгъл“, Склад А2, п.к.  
4006, гр. Пловдив, България  
[www.enapart.bg](http://www.enapart.bg)  
[sales@enapart.bg](mailto:sales@enapart.bg)



3 Austin Mews, High Street, Hemel  
Hempstead, HP1 3AF , United Kingdom  
[www.enapart.co.uk](http://www.enapart.co.uk)  
[sales@enapart.co.uk](mailto:sales@enapart.co.uk)

## Marbett

Enapart always strives to provide the competitive prices and timings of supplies for its customers. We sell only original equipment and spare parts, although we are not always the official distributor or manufacturer's dealer. All displayed trademarks and part numbers are the property of their respective owners.

### BRAND'S PRODUCTS

Product	Description
<a href="#">31000YAT208</a>	Y-bearing
<a href="#">Cod. S0771UL626363N</a>	NECK GUIDE
<a href="#">SUPP BASE TRIPOD 615 D48.3MM PA SS</a>	Supporting element
<a href="#">S0567677322</a>	
<a href="#">S0569677332</a>	ROL-PLT 569 END L115MM M5X16MM HP
<a href="#">S0568677312</a>	roller transfer module
<a href="#">S027366791</a>	
<a href="#">B000063112</a>	bearing
<a href="#">S036669585M</a>	GUIDE
<a href="#">S0581603312</a>	
<a href="#">S007150960</a>	GUIDE HOLDER CLAMP D12
<a href="#">S0110750710N</a>	Railing holder with cross handle
<a href="#">S0000607963</a>	
<a href="#">S0000607923</a>	
<a href="#">S0000644633</a>	
<a href="#">S0786621783</a>	balustrade connector
<a href="#">S021159961</a>	GUIDE CLAMP PLASTIC
<a href="#">R0869618973</a>	
<a href="#">S0159622381</a>	
<a href="#">B000068349 --- FL1206-30-PA-OP</a>	
<a href="#">L0820662091 NT820-21T-25MM-I-PA</a>	
<a href="#">S022361031 (tot. 24.00mt)</a>	
<a href="#">S0422-512</a>	
<a href="#">R0408678801N1</a>	
<a href="#">B000068349</a>	
<a href="#">L0820662091</a>	
<a href="#">S0340627051</a>	CROSS CLAMP
<a href="#">B0000681952</a>	
<a href="#">S0688684552</a>	
<a href="#">S0562697861</a>	
<a href="#">S0756645133</a>	
<a href="#">S0788615503</a>	
<a href="#">S028063503</a>	BEARING HEAD
<a href="#">S0618638812</a>	SUPP BASE BIPOD
<a href="#">S0599613572</a>	Bracket
<a href="#">S033760334N</a>	HINGE

Product	Description
<a href="#">S0581603322</a>	
<a href="#">R0133633252</a>	Leveler Product Series 133
<a href="#">R0000630052</a>	ANTI SLIP
<a href="#">R0869619253</a>	
<a href="#">B0000648091</a>	
<a href="#">B0000648101</a>	
<a href="#">S0615624262</a>	
<a href="#">S0082P6184910</a>	GUIDE RAIL CLAMP
<a href="#">S023763151</a>	
<a href="#">S001851490</a>	Nozzle shell
<a href="#">S001951460</a>	Nozzle conical
<a href="#">S007150970</a>	GUIDE RAIL CLAMP
<a href="#">S0637648382</a>	
<a href="#">S0107655522N</a>	
<a href="#">S042265248M</a>	CHAIN GUIDE
<a href="#">S036664056M</a>	CHAIN GUIDE
<a href="#">S0550689491</a>	CHAIN INLET GUIDE
<a href="#">S042265248M</a>	
<a href="#">S042265258M</a>	
<a href="#">S008250940</a>	
<a href="#">10402843</a>	
<a href="#">R0133633222</a>	
<a href="#">S0296618291</a>	
<a href="#">L0821665721</a>	
<a href="#">L0821648082</a>	
<a href="#">L0821603951</a>	
<a href="#">S035661605</a>	
<a href="#">S0822632723</a>	
<a href="#">S021560121N</a>	
<a href="#">R0224617632</a>	
<a href="#">10177755</a>	
<a href="#">RMB S0581603312</a>	
<a href="#">S0537689231</a>	
<a href="#">S0535684641</a>	
<a href="#">S0107S643543</a>	
<a href="#">S006166194N</a>	
<a href="#">10324477</a>	
<a href="#">10148199</a>	
<a href="#">10091050</a>	
<a href="#">10372197</a>	
<a href="#">S0233689371</a>	
<a href="#">91070191</a>	
<a href="#">S024363701</a>	CHN GUIDE
<a href="#">S0565698681</a>	EXP PLUG
<a href="#">S0153684231N1</a>	WEAR SHOE

Product	Description
<a href="#">L1080WSS- W1080 SS</a>	catenary\ conveyor belt
<a href="#">S0153684231N1</a>	
<a href="#">S0569605922</a>	ROL-PLT 569 END L85MM HP
<a href="#">S023663931</a>	
<a href="#">S0107655522</a>	
<a href="#">S0757645093</a>	
<a href="#">S0760613443</a>	
<a href="#">R0297629212N1</a>	machine base
<a href="#">B0000646511</a>	.
<a href="#">S0765608943N</a>	CHAIN
<a href="#">S0210P6185510</a>	Triple foot
<a href="#">10324478</a>	
<a href="#">S037963656</a>	
<a href="#">S0704 684892</a>	
<a href="#">S0537689231</a>	METAL-PROF 537 SS 40X8MM L3209MM
<a href="#">S0341627081</a>	CLAMP PH-CELL 341 D14MM S12MM PA ZN
<a href="#">R022463001</a>	TUBE END SQR 224 L50X2.5MM M20
<a href="#">S010767821N</a>	
<a href="#">S022361031 (1 pc = 3.05 m)</a>	Guides
<a href="#">S022361743</a>	Guide
<a href="#">S0705684912</a>	LATERAL SUPPORT WITHOUT SUPPORTING EDGE MS.705
<a href="#">S033968363</a>	T-Clamp
<a href="#">S034168383</a>	Clamp
<a href="#">S0341C6721500</a>	CLAMP REFLECT
<a href="#">R032361404N</a>	joint foot
<a href="#">69026</a>	
<a href="#">651072</a>	
<a href="#">S033767023N</a>	Hinge
<a href="#">RMB S010768200N</a>	SUPPORT
<a href="#">S037261826</a>	
<a href="#">S0518642951N</a>	
<a href="#">S0518696021N</a>	
<a href="#">S0174652452</a>	
<a href="#">S0082P6184910</a>	GUIDE RAIL CLAMP
<a href="#">S0763610593</a>	
<a href="#">R0323626993</a>	
<a href="#">R0098626122</a>	
<a href="#">S0732692362N</a>	Cross clamp
<a href="#">S025664561</a>	Swivel head
<a href="#">B0000666962</a>	Bearing
<a href="#">S0556695231</a>	
<a href="#">825</a>	
<a href="#">S024263671</a>	
<a href="#">623/649892</a>	feet gripper
<a href="#">R0623643742</a>	

Product	Description
<a href="#">S0567688792</a>	ROL-PLT 567 LIP3 L85MM HP
<a href="#">S0568605912</a>	
<a href="#">S017459301</a>	
<a href="#">627031, S0340</a>	Cross clamp
<a href="#">S0339626001</a>	Clamp
<a href="#">S0153608692N1</a>	Chains pieces
<a href="#">S0551689501</a>	Chain inlet shoe left + right.
<a href="#">S0153608692N1</a>	
<a href="#">S0560697551</a>	Roll
<a href="#">S033967365</a>	
<a href="#">S02756681</a>	G-RAIL CLAMP
<a href="#">S0275664151</a>	GUIDE RAIL CLAMP
<a href="#">B000068533</a>	Oval carcass
<a href="#">B0000681972</a>	COVER-MB 205 25 OP SEAL
<a href="#">S0615624272</a>	Tripod base
<a href="#">S0198664761</a>	Support head
<a href="#">S0210P 6203910 (1 meter)</a>	Guide clamp
<a href="#">S0661675722</a>	
<a href="#">S026066556</a>	
<a href="#">S0770609183N (1 meter)</a>	
<a href="#">S0770609203N (1 meter)</a>	
<a href="#">L1873LF623621</a>	
<a href="#">L1873604741</a>	Chain
<a href="#">114-139-6</a>	ROLLER SHUTTER
<a href="#">B0000697752</a>	
<a href="#">B0000697772</a>	
<a href="#">S0699684872</a>	
<a href="#">R0098626693</a>	
<a href="#">S010750710N</a>	SUPPORT WITH HANDLE DF12
<a href="#">R034965634N1</a>	
<a href="#">R022459251</a>	
<a href="#">R0098626042</a>	
<a href="#">S0734693552</a>	
<a href="#">S0732692352N</a>	
<a href="#">S0645652352</a>	
<a href="#">S000068309</a>	
<a href="#">S0568687402</a>	Modular transfer roller plate
<a href="#">SO26263651</a>	
<a href="#">S0734693562</a>	
<a href="#">S0732692372N</a>	
<a href="#">S0075672652N</a>	
<a href="#">R034964045N1</a>	
<a href="#">S0768609113N</a>	SIDE GUIDES
<a href="#">S0210600372</a>	
<a href="#">S0708605603</a>	

Product	Description
<a href="#">RMB S0569605922</a>	Roller Trasfer Conveyor
<a href="#">787.01.09</a>	
<a href="#">787.00.87</a>	
<a href="#">B0000686602</a>	
<a href="#">S027566811</a>	guide holder clamp
<a href="#">S0537689231</a>	
<a href="#">R0408678821N1</a>	
<a href="#">S012665396</a>	
<a href="#">S0727688902</a>	Roller
<a href="#">762.33.421</a>	Chain
<a href="#">S0564698551</a>	Connecting Joint
<a href="#">S0618624322</a>	Support base bipod
<a href="#">S021159961</a>	Guide holder clamp
<a href="#">S0612619452</a>	Lock ring
<a href="#">S034660204</a>	
<a href="#">S0903656001N</a>	Guide holder clamp
<a href="#">S037261786</a>	
<a href="#">S0902656041</a>	clamp
<a href="#">S0765608973</a>	GUIDE
<a href="#">S0210P6203910</a>	CLAMP
<a href="#">S082P6184910</a>	
<a href="#">S0676689692</a>	Clamp
<a href="#">S0661683802</a>	
<a href="#">S000065624</a>	
<a href="#">S0683684442</a>	
<a href="#">S0654UL691722</a>	
<a href="#">S0903656001N</a>	clamp
<a href="#">S021961753</a>	
<a href="#">S0903656001N</a>	clamp
<a href="#">S0075672662N</a>	
<a href="#">S0075672672N</a>	
<a href="#">S024763911</a>	G-RAIL 247 ROUND GN SS T1.5MM L3.05M
<a href="#">S011651590</a>	GUIDE RAIL CLAMP 111 PIN12MM
<a href="#">S0107S643533</a>	BRKT 107S D12MM LA9MM PA W/O LIP
<a href="#">S0107S643553</a>	BRKT 107S D12MM LA10.5MM PA W/O LIP
<a href="#">S0637648392</a>	
<a href="#">S0637648372</a>	
<a href="#">182-54911 - S018254911</a>	Knob part
<a href="#">S0174646481</a>	
<a href="#">S0595610452</a>	
<a href="#">S0079672632</a>	
<a href="#">S0079672622</a>	
<a href="#">R0323626612</a>	
<a href="#">S034168395</a>	clamp
<a href="#">S034068385</a>	

Product	Description
<a href="#">S033968375</a>	
<a href="#">S021360091</a>	GUIDE HOLDER CLAMP D12
<a href="#">S029860362</a>	
<a href="#">S010750710</a>	Side mounting bracket
<a href="#">R0173625362</a>	
<a href="#">S0214</a>	
<a href="#">R032361414N</a>	articular foot
<a href="#">S021460111</a>	
<a href="#">S0214644293</a>	
<a href="#">S0192674022</a>	
<a href="#">S0678684292</a>	
<a href="#">S0848645643</a>	
<a href="#">S0539689301</a>	
<a href="#">S015969130</a>	
<a href="#">R032362313N</a>	
<a href="#">S0580603292</a>	Roller guide
<a href="#">S0075672642N</a>	Winding Tensioner
<a href="#">S0825632033</a>	
<a href="#">S0524643501</a>	
<a href="#">S0533672801</a>	
<a href="#">S0523643451</a>	
<a href="#">754.60.52</a>	
<a href="#">B000063172</a>	
<a href="#">S031769072</a>	
<a href="#">S027366791</a>	
<a href="#">S0581603312</a>	SIDE ROLLER GUIDE
<a href="#">S027367602</a>	
<a href="#">S0692686302N</a>	
<a href="#">S021860151</a>	
<a href="#">S0617613562</a>	BRACKET WITH TIE ROD
<a href="#">S030360872</a>	
<a href="#">S0182649961N</a>	
<a href="#">S034068373</a>	
<a href="#">S017457941</a>	nut
<a href="#">S0339627011</a>	T-CLAMP 339 D12MMXS10MM PA ZN
<a href="#">FG500XLG 0110mm</a>	
<a href="#">S022664631N</a>	
<a href="#">S033867563</a>	
<a href="#">L0820603761</a>	
<a href="#">L0820603811</a>	
<a href="#">762.53.722</a>	
<a href="#">762.53.312</a>	
<a href="#">L0820661911</a>	
<a href="#">L0820661471</a>	
<a href="#">S0616624552</a>	

Product	Description
<a href="#">S0563697891</a>	
<a href="#">R0749602093</a>	
<a href="#">S0567687382</a>	
<a href="#">S019859161</a>	top bracket
<a href="#">R0098626022</a>	
<a href="#">R0169624862</a>	
<a href="#">S034067375</a>	
<a href="#">COVER-MB 206 30 CL O</a>	CLOSED COVER
<a href="#">COVER-MB 206 30 OP SEAL</a>	OPEN COVER
<a href="#">S012864521</a>	ROLLER
<a href="#">S034167385</a>	
<a href="#">R0173625412</a>	spindle
<a href="#">R0173626673</a>	spindle
<a href="#">S0192608683</a>	
<a href="#">S0185683902</a>	handwheel
<a href="#">S017453781</a>	CROSS CLAMP 174 D16X16MM PA
<a href="#">S0580603302</a>	SIDE ROLLER GUIDE
<a href="#">S015957211</a>	
<a href="#">UCFB 208 C 601143</a>	Side flanged supports
<a href="#">UCFB 208 C 601163</a>	Side flanged supports
<a href="#">S0634634073</a>	
<a href="#">B000068399</a>	
<a href="#">B000069016</a>	flanged bearing
<a href="#">B000069026</a>	flanged bearing
<a href="#">S0367 64046M</a>	Sliding guide
<a href="#">LEV297-M30X190MM-27-ZN-PA</a>	
<a href="#">S0621 635542</a>	Block connecting,
<a href="#">S006150870N</a>	SPACER
<a href="#">601373N</a>	
<a href="#">601393N</a>	
<a href="#">R0406-66614</a>	
<a href="#">R0622643572</a>	
<a href="#">S022667305N</a>	
<a href="#">S0612640602</a>	
<a href="#">R022468607</a>	
<a href="#">S0637648382</a>	
<a href="#">S033968363</a>	
<a href="#">S0261UL634533N</a>	Chain Guide
<a href="#">S0840UL642693</a>	
<a href="#">R0134627423</a>	
<a href="#">R0297629192N1</a>	
<a href="#">S0185698942</a>	
<a href="#">S0192674012</a>	
<a href="#">B000064058</a>	flange bearing
<a href="#">B000063154</a>	



Product	Description
<a href="#">B000069965</a>	
<a href="#">10759109</a>	
<a href="#">10759111</a>	
<a href="#">B0000646592</a>	
<a href="#">S0715UL691892N</a>	
<a href="#">SHCFLS208C-40-PASS-OP-O</a>	
<a href="#">S0107650453N</a>	
<a href="#">S0755645113</a>	
<a href="#">902-656041</a>	
<a href="#">S0455614381</a>	ROLLER
<a href="#">S0685684502</a>	
<a href="#">R0408678851N1</a>	
<a href="#">B000068399 / UCFL206C-30-PA-CL-O</a>	
<a href="#">B000068409 / UCFL206C-30-PA-OP-O</a>	
<a href="#">612-692942</a>	Square Bore Split Shaft Collar Without Keyway
<a href="#">S017453791</a>	Cross clamp
<a href="#">S0757645083</a>	
<a href="#">S0612655132</a>	
<a href="#">S0768609083N</a>	CLAMP
<a href="#">S0555695211</a>	
<a href="#">S0554695171</a>	
<a href="#">S0556695251</a>	
<a href="#">S0729689642</a>	
<a href="#">S0729697662</a>	
<a href="#">B0000674502</a>	SUPPORT
<a href="#">S018254911</a>	Knob part 182 M10-nut
<a href="#">S0661675732</a>	
<a href="#">S0000638413</a>	EYE PULLER
<a href="#">S0770609183N</a>	
<a href="#">S0557 603482</a>	Central guide with rollers
<a href="#">R034963747N1</a>	
<a href="#">96/83237</a>	
<a href="#">R034963747N1 (package of 16 pcs)</a>	
<a href="#">B000065901</a>	
<a href="#">B000061819</a>	
<a href="#">S026065031</a>	Hinge
<a href="#">S026066566</a>	Hinge
<a href="#">S0082P6827820</a>	Guide clamp
<a href="#">S0255-69680</a>	
<a href="#">S0632- 605263</a>	
<a href="#">S0632647142</a>	
<a href="#">S018553081</a>	Knob part
<a href="#">S019253091</a>	Clamp
<a href="#">S0210P6203910</a>	Clamp
<a href="#">R0323679061N</a>	adjustable feet

Product	Description
<a href="#">R032365596N</a>	adjustable feet
<a href="#">S0771UL626363N</a>	
<a href="#">S017453791 ( 15X15 )</a>	Cross connection clamp
<a href="#">S0786622423</a>	
<a href="#">NST820-21T-40MM-I-PA</a>	
<a href="#">S035661605 UH-T-2-25, PN: 514-176-1</a>	
<a href="#">S0765608973N</a>	
<a href="#">B0000 64018</a>	
<a href="#">B0000 64028</a>	
<a href="#">S000065794</a>	PIN Dia. 12mm x 118mm SS M10x18
<a href="#">S0182645141N</a>	Tightening Knob
<a href="#">R0133627232</a>	
<a href="#">S021360101</a>	Double clamp no pin
<a href="#">S018354921</a>	Tightening knob Marbett 183 M1
<a href="#">R070163033</a>	
<a href="#">S0000644613</a>	roller rail
<a href="#">S0595 610442 T CLAMP</a>	
<a href="#">B000063232</a>	COVER
<a href="#">B0000646652</a>	
<a href="#">S033767023</a>	
<a href="#">UCFL204C-20-PA-open</a>	
<a href="#">B0000680942</a>	
<a href="#">B0000681002</a>	
<a href="#">UCFL205C-25-PA-open</a>	
<a href="#">S012864511</a>	
<a href="#">68976</a>	
<a href="#">B0000672411</a>	
<a href="#">B0000697752 / SHCFL208C-40-PA-CL-O</a>	
<a href="#">S0082P6185110</a>	
<a href="#">B0000672421</a>	
<a href="#">P615-B48,3</a>	
<a href="#">P98-S14-M16x95-ZN</a>	
<a href="#">B000068563</a>	
<a href="#">R0098626102</a>	
<a href="#">B0000646552</a>	
<a href="#">S030260962</a>	
<a href="#">S030360942</a>	
<a href="#">S0683684462</a>	
<a href="#">S009551380</a>	
<a href="#">B000068986</a>	FL 1204 open oval flange mount
<a href="#">Cod. R022463001</a>	
<a href="#">S021960161</a>	SIDE GUIDE
<a href="#">S0736695402</a>	JOINT CLAMP
<a href="#">S0551630913</a>	
<a href="#">S0551630923</a>	

Product	Description
<a href="#">S010768200</a>	
<a href="#">S0082B6827620</a>	
<a href="#">646532 / UCP208-40-PA-SS</a>	
<a href="#">63549</a>	
<a href="#">S037164026</a>	
<a href="#">S017969523</a>	
<a href="#">S022369402</a>	SIDE GUIDE
<a href="#">B0000656552N</a>	
<a href="#">B000064573</a>	
<a href="#">B000064623</a>	
<a href="#">S024163641</a>	Wear Strip - Chain Guide, type:L green, P/N 251, code:63641
<a href="#">R0323626602</a>	
<a href="#">S019260933</a>	Adjustable head
<a href="#">R0726688772</a>	spacer
<a href="#">S025664571</a>	
<a href="#">S025664581</a>	
<a href="#">S026165681 / P261-Zlprof-20x3-gr</a>	
<a href="#">S012864541</a>	Roller railing
<a href="#">S012864481</a>	Roller railing
<a href="#">S0760613433</a>	lateral wedge module
<a href="#">S0852646633</a>	